


\rightarrow For small blind corners






	94°
Cup fixing	Drilling pattern 48/6
For screw fixing	329.34.600
Packing: 1 or 50 pieces	

Order reference

Only suitable for mounting plate 329.88.609 with drill hole 28 x 32 mm

CAD


≥32



Mounting plate distance 9 mm

\rightarrow For large blind corners







	110°
Cup fixing	Drilling pattern 48/6
For screw fixing	329.35.600
Packing: 1 or 50 pieces	

Packing: 1 or 50 pieces

Order reference


Suitable for all Duomatic A and Duomatic SM mounting plates






Mounting plate distance 0 mm

X max.: For Duomatic A = 61 mm For Duomatic SM = 70 mm For Duomatic SM with rear eccentric = 74 mm E = distance to cup



Mounting plate distance 3 mm



Mounting plate distance 6 mm

Drilling patterns/technical information	►FF 4.8
Mounting plates	►FF 4.48